



HSR14T48PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR14T48PF](#)

.25" ID Min (Expanded), .13" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 4-Foot Reel

Features

- Heat Shrink Tubing
- .25" ID Min (Exp), .12" ID Max (Red)
- #14-#10, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#14 AWG to #10 AWG
Conductor Size	14AWG - 10AWG

Configuration

Connector Type	THIN WALL REEL
Dimensions	
Width	0.25 in
Height	0.25 in
Length	48 in
Dimensions	48 in x 0.25 in x 0.25 in
General	
Material	Cross-linked Polyolefin
UPC	781810212554
Color	Red
Logistics	
Minimum Pack Quantity	1
Product Assets	
Catalog [English]	