



HSR18FR, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR18FR](#)



.13" ID Min (Expanded), .06" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	16AWG - 14AWG
Conductor Range	#16 AWG to #14 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Height	0.125 in
Width	0.125 in
Length	600 in
Dimensions	600 in x 0.125 in x 0.125 in

General

Color	Red
UPC	781810266687
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	48
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)