



HSR18T300PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR18T300PF](#)

.13" ID Min (Expanded), .06" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 25-Foot Reel

Features

- Heat Shrink Tubing
- .13" ID Min (Exp), .06" ID Max (Rec)
- #18-#14, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#18 AWG to #14 AWG
Conductor Size	18AWG - 14AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.125 in
Height	0.125 in
Length	300 in
Dimensions	300 in x 0.125 in x 0.125 in

General

Material	Cross-linked Polyolefin
UPC	781810213476
Color	Red

Logistics

Minimum Pack Quantity	10
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)