



HSR18T48PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy  
Catalog # [HSR18T48PF](#)

.13" ID Min (Expanded), .06" ID Max (Recovered), Fire Retardant, Thin Wall, Red, 4-Foot Reel

Features

- Heat Shrink Tubing
- .13" ID Min (Exp), .06" ID Max (Rec)
- #18-#14, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| UL Listed                          | No  |
| Certification - ETL                | No  |
| Standards - RoHS Compliance Status | CM  |

Conductor

|                 |                    |
|-----------------|--------------------|
| Conductor Range | #18 AWG to #14 AWG |
| Conductor Size  | 18AWG - 14AWG      |

Configuration

|                |                |
|----------------|----------------|
| Connector Type | THIN WALL REEL |
|----------------|----------------|

Dimensions

|            |                             |
|------------|-----------------------------|
| Width      | 0.125 in                    |
| Height     | 0.125 in                    |
| Length     | 48 in                       |
| Dimensions | 48 in x 0.125 in x 0.125 in |

General

|          |                         |
|----------|-------------------------|
| Material | Cross-linked Polyolefin |
| UPC      | 781810212394            |
| Color    | Red                     |

Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
| Carton Quantity       | 1  |
| Pallet Quantity       | 1  |

Product Assets

[Catalog \[English\]](#)