



HSR38FR, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR38FR](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 50-Foot Reel

Features

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	6AWG -4AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Dimensions

Width	0.375 in
Height	0.375 in
Length	600 in
Dimensions	600 in x 0.375 in x 0.375 in

General

Material	Polyvinyl chloride
UPC	781810266779
Color	Red

Logistics

Minimum Pack Quantity	32
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)