



HSR38FR250, Heat Shrink Tubing PVC, Thin Wall, FR, Red

By Burndy
Catalog # [HSR38FR250](#)



.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 250-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, PVC, Fire Retardant
- Thin Wall, Red
- 250 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Size	6AWG -4AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL TUBES/REELS
----------------	-----------------------

Current

Voltage Rating	600 V
----------------	-------

Dimensions

Height	0.375 in
Width	0.375 in
Length	3000 in
Dimensions	3000 in x 0.375 in x 0.375 in

General

Product Type	PVC Thin Wall Heat Shrink
Color	Red
UPC	781810266830
Material	Polyvinyl chloride

Logistics

Minimum Pack Quantity	4
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)