



HSR38T1200PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR38T1200PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 100-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 100 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	Yes

Conductor

Conductor Range	#8 AWG to #6 AWG
-----------------	------------------

Dimensions

Height	0.375 in
Width	0.375 in
Length	1200 in
Dimensions	1200 in x 0.375 in x 0.375 in

General

Color	Red
UPC	781810242605
Material	Polyolefin

Logistics

Minimum Pack Quantity	10
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)