



HSR38T300PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR38T300PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 25-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 25 Foot Reel

Specifications

Certification - CSA Approved	Yes
UL Listed	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM

Conductor

Conductor Range	#8 AWG to #6 AWG
Conductor Size	8AWG - 6AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Width	0.375 in
Height	0.375 in
Length	300 in
Dimensions	300 in x 0.375 in x 0.375 in

General

Material	Cross-linked Polyolefin
UPC	781810213681
Color	Red

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)



A Hubbell brand