



HSR38T48PF, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSR38T48PF](#)

.38" ID Min (Expanded), .19" ID Max (Recovered), Thin Wall, Fire Retardant, Red, 4-Foot Reel

Features

- Heat Shrink Tubing
- .38" ID Min (Exp), .19" ID Max (Rec)
- #8-#6, Polyolefin, Thin Wall, Red
- Shrink Ratio 2:1
- 4 Foot Reel

Specifications

Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	Yes
UL Listed	No

Conductor

Conductor Size	8AWG - 6AWG
Conductor Range	#8 AWG to #6 AWG

Configuration

Connector Type	THIN WALL REEL
----------------	----------------

Dimensions

Length	48 in
Width	0.375 in
Height	0.375 in
Dimensions	48 in x 0.375 in x 0.375 in

General

Color	Red
Material	Cross-linked Polyolefin
UPC	781810212622

Logistics

Minimum Pack Quantity	10
Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)