



HSTPBK0063100FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK0063100FRL](#)

.063" ID Min (Issued), .031" ID Max (Recovered), Thin Wall, Black, 100-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height 0.017 in

Width 0.063 in
Length 1200 in
Dimensions 1200 in x 0.063 in x 0.017 in

General

Color Black
UPC 621945690622

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)