



HSTPBK006350FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK006350FRL](#)



.063" ID Min (Issued), .031" ID Max (Recovered), Thin Wall, Black, 50-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height	0.017 in
Width	0.063 in
Length	600 in
Dimensions	600 in x 0.063 in x 0.017 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	Black
UPC	621945690639

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog \[English\]](#)