



HSTPBK00941000FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK00941000FRL](#)

.094" ID Min (Issued), .047" ID Max (Recovered), Thin Wall, Black,
1000-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height	0.02 in
Width	0.094 in

Length	12000 in
Dimensions	12000 in x 0.094 in x 0.02 in

General

Color	Black
UPC	621945691247

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)