



HSTPBK00946IPK25, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK00946IPK25](#)

.094" ID Min (Issued), .047" ID Max (Recovered), Thin Wall, Black,
6" Lengths, 25 Pieces per package

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height 0.02 in



Width 0.094 in
Length 6 in
Dimensions 6 in x 0.094 in x 0.02 in

General

Color Black
UPC 621945691223

Logistics

Carton Quantity 80

Product Assets

[Catalog \[English\]](#)