



HSTPBK0187100FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK0187100FRL](#)

.187" ID Min (Issued), .093" ID Max (Recovered), Thin Wall, Black, 100-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating600 V

Dimensions

Height0.02 in



Width0.187 in
Length1200 in
Dimensions1200 in x 0.187 in x 0.02 in

General

Product TypePolyolefin Thin Wall Heat Shrink
ColorBlack
UPC621945692640

Logistics

Pallet Quantity180
Carton Quantity5

Product Assets

[Catalog \[English\]](#)