



# HSTPBK0250500FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy  
Catalog # [HSTPBK0250500FRL](#)

.25" ID Min (Issued), .025" ID Max (Recovered), Thin Wall, Black,  
500-Foot Reel

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Dimensions

|        |          |
|--------|----------|
| Height | 0.025 in |
| Width  | 0.25 in  |



|            |                              |
|------------|------------------------------|
| Length     | 6000 in                      |
| Dimensions | 6000 in x 0.25 in x 0.025 in |

## General

|       |              |
|-------|--------------|
| Color | Black        |
| UPC   | 621945693326 |

## Logistics

|                 |     |
|-----------------|-----|
| Pallet Quantity | 360 |
| Carton Quantity | 1   |

## Product Assets

[Catalog \[English\]](#)