



HSTPBK0375100FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK0375100FRL](#)

.375" ID Min (Issued), .187" ID Max (Recovered), Thin Wall, Black, 100-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.025 in



Width 0.375 in
Length 1200 in
Dimensions 1200 in x 0.375 in x 0.025 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Black
UPC 621945693982
Material Cross-linked Polyolefin

Logistics

Pallet Quantity 1
Carton Quantity 5

Product Assets

[Catalog \[English\]](#)