



HSTPBK1000100FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK1000100FRL](#)

1" ID Min (Issued), .50" ID Max (Recovered), Thin Wall, Black, 100-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height	0.035 in
Width	1 in

Length	1200 in
Dimensions	1200 in x 1 in x 0.035 in

General

Color	Black
UPC	621945696099
Material	Cross-linked Polyolefin

Logistics

Pallet Quantity	360
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)