



# HSTPBK100050FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy  
Catalog # [HSTPBK100050FRL](#)

1" ID Min (Issued), .50" ID Max (Recovered), Thin Wall, Black, 50-Foot Reel



### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Dimensions

|        |          |
|--------|----------|
| Height | 0.035 in |
| Width  | 1 in     |

|            |                          |
|------------|--------------------------|
| Length     | 600 in                   |
| Dimensions | 600 in x 1 in x 0.035 in |

### General

|       |              |
|-------|--------------|
| Color | Black        |
| UPC   | 621945696105 |

### Logistics

|                 |    |
|-----------------|----|
| Pallet Quantity | 48 |
| Carton Quantity | 2  |

### Product Assets

[Catalog \[English\]](#)