



HSTPBK400050FRL, Heat Shrink Tubing, Thin Wall, Black

By Burndy
Catalog # [HSTPBK400050FRL](#)

4" ID Min (Issued), 2" ID Max (Recovered), Thin Wall, Black, 50-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Width	4 in
Height	0.055 in

Length	600 in
Dimensions	600 in x 4 in x 0.055 in

General

UPC	621945697775
Color	Black

Logistics

Carton Quantity	1
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)