



# HSTPBL050025FRL, Heat Shrink Tubing, Thin Wall, Blue

By Burndy  
Catalog # [HSTPBL050025FRL](#)



.50" ID Min (Issued), .25" ID Max (Recovered), Thin Wall, Blue, 25-Foot Reel

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Current

Voltage Rating                      600 V

### Dimensions

|            |                            |
|------------|----------------------------|
| Height     | 0.025 in                   |
| Width      | 0.5 in                     |
| Length     | 300 in                     |
| Dimensions | 300 in x 0.5 in x 0.025 in |

### General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Blue                             |
| UPC          | 621945694682                     |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 8 |
|-----------------|---|

### Product Assets

[Catalog \[English\]](#)