



HSTPCL012550FRL, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSTPCL012550FRL](#)



.125" ID Min (Issued), .063" ID Max (Recovered), Thin Wall, Clear, 50-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.02 in

Width 0.0125 in
Length 600 in
Dimensions 600 in x 0.0125 in x 0.02 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Clear
UPC 621945692091

Logistics

Pallet Quantity 1
Carton Quantity 10

Product Assets

[Catalog \[English\]](#)