



# HSTPCL0250250FRL, Heat Shrink Tubing, Thin Wall, Clear

By Burndy  
Catalog # [HSTPCL0250250FRL](#)

.250" ID Min (Issued), .125" ID Max (Recovered), Thin Wall, Clear, 250-Foot Reel

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Dimensions

|        |          |
|--------|----------|
| Height | 0.025 in |
| Width  | 0.25 in  |



|            |                              |
|------------|------------------------------|
| Length     | 3000 in                      |
| Dimensions | 3000 in x 0.25 in x 0.025 in |

## General

|       |              |
|-------|--------------|
| Color | Clear        |
| UPC   | 621945693470 |

## Logistics

|                 |   |
|-----------------|---|
| Pallet Quantity | 1 |
| Carton Quantity | 2 |

## Product Assets

[Catalog \[English\]](#)