



# HSTPCL06254FPK5EA, Heat Shrink Tubing, Thin Wall, Clear

By Burndy  
Catalog # [HSTPCL06254FPK5EA](#)

.625" ID Min (Issued), .313" ID Max (Recovered), Thin Wall, Clear, 4-Foot  
Lengths, 5 Pieces per package

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Current

Voltage Rating                      600 V



## Dimensions

|        |          |
|--------|----------|
| Width  | 0.625 in |
| Length | 48 in    |

## General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Clear                            |
| UPC          | 621945699939                     |

## Product Assets

[Catalog \[English\]](#)