



# HSTPCL1000100FRL, Heat Shrink Tubing, Thin Wall, Clear

By Burndy  
Catalog # [HSTPCL1000100FRL](#)

1" ID Min (Issued), .50" ID Max (Recovered), Thin Wall, Clear, 100-Foot Reel



### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Dimensions

|        |          |
|--------|----------|
| Height | 0.035 in |
| Width  | 1 in     |

|            |                           |
|------------|---------------------------|
| Length     | 1200 in                   |
| Dimensions | 1200 in x 1 in x 0.035 in |

### General

|          |                         |
|----------|-------------------------|
| Color    | Clear                   |
| UPC      | 621945696198            |
| Material | Cross-linked Polyolefin |

### Logistics

|                 |    |
|-----------------|----|
| Pallet Quantity | 48 |
| Carton Quantity | 1  |

### Product Assets

[Catalog \[English\]](#)