



# HSTPCL400025FRL, Heat Shrink Tubing, Thin Wall, Clear

By Burndy  
Catalog # [HSTPCL400025FRL](#)

4" ID Min (Issued), 2" ID Max (Recovered), Thin Wall, Clear, 25-Foot Reel

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Current

Voltage Rating600 V

## Dimensions



|            |                          |
|------------|--------------------------|
| Height     | 0.055 in                 |
| Width      | 4 in                     |
| Length     | 300 in                   |
| Dimensions | 300 in x 4 in x 0.055 in |

## General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Clear                            |
| UPC          | 621945697843                     |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 2 |
|-----------------|---|

## Product Assets

[Catalog \[English\]](#)