



HSTPCL40004FPK2EA, Heat Shrink Tubing, Thin Wall, Clear

By Burndy
Catalog # [HSTPCL40004FPK2EA](#)

4" ID Min (Issued), 2" ID Max (Recovered), Thin Wall, Clear, 4-Foot Lengths, 2 Pieces per package

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V



Dimensions

Width 4 in
Length 48 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Clear
UPC 621945700529

Product Assets

[Catalog \[English\]](#)