



HSTPGR00631000FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSTPGR00631000FRL](#)

.063" ID Min (Issued), .031" ID Max (Recovered), Thin Wall, Green,
1000-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height	0.017 in
Width	0.063 in

Length	12000 in
Dimensions	12000 in x 0.063 in x 0.017 in

General

Color	Green
UPC	621945690837

Logistics

Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)