



# HSTPGR0063100FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy  
Catalog # [HSTPGR0063100FRL](#)



.063" ID Min (Issued), .031" ID Max (Recovered), Thin Wall, Green, 100-Foot Reel

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Current

Voltage Rating                      600 V

### Dimensions

|                |                                  |
|----------------|----------------------------------|
| Height         | 0.017 in                         |
| Width          | 0.063 in                         |
| Length         | 1200 in                          |
| Dimensions     | 1200 in x 0.063 in x 0.017 in    |
| <b>General</b> |                                  |
| Product Type   | Polyolefin Thin Wall Heat Shrink |
| Color          | Green                            |
| UPC            | 621945690868                     |

### Logistics

Carton Quantity                      5

### Product Assets

[Catalog \[English\]](#)