



HSTPGR01254FPK25EA, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSTPGR01254FPK25EA](#)

.125" ID Min (Issued), .063" ID Max (Recovered), Thin Wall, Green, 4-Foot Lengths, 25 Pieces per package

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V



Dimensions

Width 0.125 in
Length 48 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Green
UPC 621945699496

Product Assets

[Catalog \[English\]](#)