



HSTPGR0500100FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSTPGR0500100FRL](#)

.50" ID Min (Issued), .25" ID Max (Recovered), Thin Wall, Green, 100-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Width 0.5 in



Height 0.025 in
Length 1200 in
Dimensions 1200 in x 0.5 in x 0.025 in

General

UPC 621945694781
Color Green

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)