



# HSTPGR0625100FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy  
Catalog # [HSTPGR0625100FRL](#)



.625" ID Min (Issued), .313" ID Max (Recovered), Thin Wall, Green, 100-Foot Reel

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Current

Voltage Rating                      600 V

### Dimensions

|            |                              |
|------------|------------------------------|
| Height     | 0.03 in                      |
| Width      | 0.625 in                     |
| Length     | 1200 in                      |
| Dimensions | 1200 in x 0.625 in x 0.03 in |

### General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Green                            |
| UPC          | 621945695337                     |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 2 |
|-----------------|---|

### Product Assets

[Catalog \[English\]](#)