



HSTPGR0750100FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSTPGR0750100FRL](#)

.75" ID Min (Issued), .375" ID Max (Recovered), Thin Wall, Green,
100-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height 0.03 in



Width 0.75 in
Length 1200 in
Dimensions 1200 in x 0.75 in x 0.03 in

General

Color Green
UPC 621945695788

Logistics

Carton Quantity 1

Product Assets

[Catalog \[English\]](#)