



HSTPGR125050FRL, Heat Shrink Tubing, Thin Wall, Green

By Burndy
Catalog # [HSTPGR125050FRL](#)

1.25" ID Min (Issued), .625" ID Max (Recovered), Thin Wall, Green, 50-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions



Height	0.035 in
Width	1.25 in
Length	600 in
Dimensions	600 in x 1.25 in x 0.035 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	Green
UPC	621945696662

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog \[English\]](#)