



# HSTPOR004725FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy  
Catalog # [HSTPOR004725FRL](#)



25' Reel Orange Heat Shrink Tubing, 3/64" I.D., Thin Wall Polyolefin Heat Shrink 600 V

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Current

Voltage Rating 600 V

### Dimensions

Height 0.016 in

Width 0.047 in  
Length 300 in  
Dimensions 300 in x 0.047 in x 0.016 in

### General

Product Type Polyolefin Thin Wall Heat Shrink  
Color Orange  
UPC 621945689510  
Material Polyolefin

### Logistics

Carton Quantity 10

### Product Assets

[Catalog \[English\]](#)