



HSTPOR004750FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy
Catalog # [HSTPOR004750FRL](#)



50' Reel Orange Heat Shrink Tubing, 3/64" I.D., Thin Wall Polyolefin Heat Shrink 600 V

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.016 in

Width 0.047 in
Length 600 in
Dimensions 600 in x 0.047 in x 0.016 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Orange
UPC 621945689503
Material Polyolefin

Logistics

Carton Quantity 10

Product Assets

[Catalog \[English\]](#)