



HSTPOR0063100FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy
Catalog # [HSTPOR0063100FRL](#)

100' Reel Orange Heat Shrink Tubing, 1/16" I.D., Thin Wall Polyolefin
Heat Shrink 600 V

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.017 in



Width 0.063 in
Length 1200 in
Dimensions 1200 in x 0.063 in x 0.017 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Orange
UPC 621945690943
Material Polyolefin

Logistics

Carton Quantity 5

Product Assets

[Catalog \[English\]](#)