



# HSTPOR0094250FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy  
Catalog # [HSTPOR0094250FRL](#)



.094" ID Min (Issued), .047" ID Max (Recovered), Thin Wall, Orange,  
250-Foot Reel

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Current

Voltage Rating                      600 V

### Dimensions

|            |                              |
|------------|------------------------------|
| Height     | 0.02 in                      |
| Width      | 0.094 in                     |
| Length     | 3000 in                      |
| Dimensions | 3000 in x 0.094 in x 0.02 in |

### General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Orange                           |
| UPC          | 621945691582                     |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 4 |
|-----------------|---|

### Product Assets

[Catalog \[English\]](#)