



HSTPOR125050FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy
Catalog # [HSTPOR125050FRL](#)

.125" ID Min (Issued), .625" ID Max (Recovered), Thin Wall,
Orange, 50-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Height 0.035 in



Width 1.25 in
Length 600 in
Dimensions 600 in x 1.25 in x 0.035 in

General

Color Orange
UPC 621945696709

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)