



HSTPOR400050FRL, Heat Shrink Tubing, Thin Wall, Orange

By Burndy
Catalog # [HSTPOR400050FRL](#)



4" ID Min (Issued), 2" ID Max (Recovered), Thin Wall, Orange, 50-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.055 in
Width 4 in
Length 600 in
Dimensions 600 in x 4 in x 0.055 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Orange
UPC 621945697898

Logistics

Carton Quantity 1

Product Assets

[Catalog \[English\]](#)