




HSTPRD00636IPK25, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSTPRD00636IPK25](#)



25 Pack 6" Red Heat Shrink Tubing, 1/16" I.D., Thin Wall Polyolefin Heat Shrink 600 V

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height 0.017 in

Width 0.063 in
Length 6 in
Dimensions 6 in x 0.063 in x 0.017 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Red
UPC 621945690974
Material Polyolefin

Logistics

Carton Quantity 80

Product Assets

[Catalog \[English\]](#)