



HSTPRD0375250FRL, Heat Shrink Tubing, Thin Wall, Red

By Burndy
Catalog # [HSTPRD0375250FRL](#)

.375" ID Min (Issued), .187" ID Max (Recovered), Thin Wall, Red, 250-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions



Height	0.025 in
Width	0.375 in
Length	3000 in
Dimensions	3000 in x 0.375 in x 0.025 in
General	
Product Type	Polyolefin Thin Wall Heat Shrink
Color	Red
UPC	621945694323

Logistics

Carton Quantity 2

Product Assets

[Catalog \[English\]](#)