



# HSTPRD050025FRL, Heat Shrink Tubing, Thin Wall, Red

By Burndy  
Catalog # [HSTPRD050025FRL](#)



.50" ID Min (Issued), .25" ID Max (Recovered), Thin Wall, Red, 25-Foot Reel

### Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

### Dimensions

|        |          |
|--------|----------|
| Height | 0.025 in |
| Width  | 0.5 in   |

|            |                            |
|------------|----------------------------|
| Length     | 300 in                     |
| Dimensions | 300 in x 0.5 in x 0.025 in |

### General

|       |              |
|-------|--------------|
| Color | Red          |
| UPC   | 621945694927 |

### Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 1008 |
| Carton Quantity | 8    |

### Product Assets

[Catalog \[English\]](#)