



# HSTPRD1500100FRL, Heat Shrink Tubing, Thin Wall, Red

By Burndy  
Catalog # [HSTPRD1500100FRL](#)

1.5" ID Min (Issued), .75" ID Max (Recovered), Thin Wall, Red, 100-Foot Reel

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Dimensions

|        |         |
|--------|---------|
| Height | 0.04 in |
| Width  | 1.5 in  |



|            |                            |
|------------|----------------------------|
| Length     | 1200 in                    |
| Dimensions | 1200 in x 1.5 in x 0.04 in |

## General

|       |              |
|-------|--------------|
| Color | Red          |
| UPC   | 621945697058 |

## Logistics

|                 |   |
|-----------------|---|
| Pallet Quantity | 1 |
| Carton Quantity | 1 |

## Product Assets

[Catalog \[English\]](#)