



HSTPWH009425FRL, Heat Shrink Tubing, Thin Wall, White

By Burndy
Catalog # [HSTPWH009425FRL](#)

.094" ID Min (Issued), .047" ID Max (Recovered), Thin Wall, White, 25-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating600 V

Dimensions

Height0.02 in



Width0.094 in
Length300 in
Dimensions300 in x 0.094 in x 0.02 in

General

Product TypePolyolefin Thin Wall Heat Shrink
ColorWhite
UPC621945691773

Logistics

Pallet Quantity1
Carton Quantity10

Product Assets

[Catalog \[English\]](#)