



# HSTPWH01251000FRL, Heat Shrink Tubing, Thin Wall, White

By Burndy  
Catalog # [HSTPWH01251000FRL](#)

.125" ID Min (Issued), .063" ID Max (Recovered), Thin Wall, White, 1000-Foot Reel

## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Current

Voltage Rating                      600 V

## Dimensions



|            |                                |
|------------|--------------------------------|
| Height     | 0.02 in                        |
| Width      | 0.0125 in                      |
| Length     | 12000 in                       |
| Dimensions | 12000 in x 0.0125 in x 0.02 in |

## General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | White                            |
| UPC          | 621945692374                     |

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Catalog \[English\]](#)