



HSTPWH200025FRL, Heat Shrink Tubing, Thin Wall, White

By Burndy
Catalog # [HSTPWH200025FRL](#)



2" ID Min (Issued), 1" ID Max (Recovered), Thin Wall, White, 25-Foot Reel

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height	0.045 in
Width	2 in
Length	300 in
Dimensions	300 in x 2 in x 0.045 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	White
UPC	621945697478

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Catalog \[English\]](#)