



HSTPWH300025FRL, Heat Shrink Tubing, Thin Wall, White

By Burndy
Catalog # [HSTPWH300025FRL](#)

3" ID Min (Issued), 1.5" ID Max (Recovered), Thin Wall, White, 25-Foot
Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 2:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V

Dimensions

Height	0.05 in
Width	3 in
Length	300 in
Dimensions	300 in x 3 in x 0.05 in

General

Product Type	Polyolefin Thin Wall Heat Shrink
Color	White
UPC	621945697720

Logistics

Carton Quantity	2
-----------------	---

Product Assets

[Catalog \[English\]](#)