



HSTPYG012525FRL, Heat Shrink, Thin Wall, Yellow/Green

By Burndy
Catalog # [HSTPYG012525FRL](#)

.125" ID Min (Issued), .063" ID Max (Recovered), Thin Wall,
Yellow/Green, 25-Foot Reel



Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 3:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Dimensions

Width	0.125 in
Height	0.02 in

Length	300 in
Dimensions	300 in x 0.125 in x 0.02 in

General

UPC	621945692572
Color	Yellow/Green

Logistics

Carton Quantity	10
Pallet Quantity	540

Product Assets

[Catalog \[English\]](#)