



**HSTPYG012550FRL, Heat Shrink, Thin Wall,  
Yellow/Green**

By Burndy

Catalog # **HSTPYG012550FRL**

.125" ID Min (Issued), .063" ID Max (Recovered), Thin Wall,  
Yellow/Green, 50-Foot Reel



## Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 3:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

## Current

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

## Dimensions

|            |                              |
|------------|------------------------------|
| Height     | 0.02 in                      |
| Width      | 0.0125 in                    |
| Length     | 600 in                       |
| Dimensions | 600 in x 0.0125 in x 0.02 in |

## General

|              |                                  |
|--------------|----------------------------------|
| Product Type | Polyolefin Thin Wall Heat Shrink |
| Color        | Yellow/Green                     |
| UPC          | 621945692565                     |

## Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

## Product Assets

[Catalog \[English\]](#)

**A Hubbell brand**