



HSTPYG02504FPK25EA, Heat Shrink, Thin Wall, Yellow/Green

By Burndy
Catalog # [HSTPYG02504FPK25EA](#)

.25" ID Min (Issued), .125" ID Max (Recovered), Thin Wall, Yellow/Green,
4-Foot Lengths, 25 Pieces per package

Features

- Ideal for industrial and automotive applications as well as covering copper and aluminum tubular connectors
- Provides mechanical protection for terminal strain relief and wire bonding
- 3:1 shrink ratio for faster shrink recovery
- Continuous Operating Temperature: -55°C to 135°C (-67°F to 275°F)
- Shrink temperature of 90°C
- Resistant to common fluids and solvents

Current

Voltage Rating 600 V



Dimensions

Width 0.25 in
Length 48 in

General

Product Type Polyolefin Thin Wall Heat Shrink
Color Yellow/Green
UPC 621945699724

Product Assets

[Catalog \[English\]](#)